

**Data sheet of Dye Laser from Sirah, pumped by INNOSLAB Lasers from EdgeWave**

**Dye laser pumped by IS8II-E, 10W @ 1kHz and 523nm**

Dye	Output power	Wavelength	Pulse Frequency
Rhodamine 6G	1,4 W	566nm	1kHz
SHG	320mW	283nm	1kHz

**Dye laser pumped by IS8III-E, 3.6W @ 1kHz and 349nm**

Dye	Output power	Wavelength	Pulse Frequency
Coumarin 47	550mW	460nm	1 kHz
SHG	82mW	230nm	1 kHz

**Dye laser pumped by IS8III-E, 3.6W @ 1kHz and 349nm**

Dye	Output power	Wavelength	Pulse Frequency
Exalite 411	520mW	414nm	1 kHz
SHG	17mW	207nm	1 kHz